FROM A CHART FROM MANUFACTURER DISSOLVE RATE

TEMPERATURE F	DIAMETER DEGRADATION RATE (IN/HR)
200	-1/128

-1/64 220 -1/16 275 300 -5/32 -9/32 325 350 -9/16

Pressure Limitation Curve Integrity vs Diameter

DALL BIANCETER	DD = 0.01 ID =
BALL DIAMETER	PRESSURE

0-1-1/2" **GREATER THAN 15K**

1-1/2" 15K 12.2K 2" 2-1/2" 10.4K 8.8K 3-1/2" 7.5K 4" 6.3K 4-1/2' 5.25K 4.5K

BALLS WERE TESTED ON SEATS 1/8" SMALLER